


各封装类型产品包装方式

TO-252封装包装方式


Packing Information-[TO-252-2L]

Packaging	Part Number	Quantity(pcs)	Size(mm)
Tube	Tube	80	L540×W20×H5
	Inner Box	4000	L570×W115×H55
	Outer Box	20000	L595×W320×H135
Reel	Reel	3000	Φ330×THK17
	Inner Box	3000	L350×W340×H25
	Outer Box	30000	L355×W300×H360

Packaging:Tube



Packaging:Reel




TO-251-3L/TO-251-2L包装方式

Packing Information-[TO-251-3L|TO-251-2L]

Packaging	Part Number	Quantity(pcs)	Size(mm)
Tube	Tube	80	L540×W20×H5
	Inner Box	4000	L570×W115×H55
	Outer Box	20000	L595×W320×H135

Packaging:Tube




TO-263-2L包裝方式


Packing Information-[TO-263-2L]

Packaging	Part Number	Quantity(pcs)	Size(mm)
Tube	Tube	50	L534×W33×H7
	Inner Box	1000	L560×W150×H40
	Outer Box	5000	L565×W235×H175
Reel	Reel	800	Φ330×THK25
	Inner Box	800	L355×W335×H35
	Outer Box	8000	L385×W365×H365

Packaging:Tube



Packaging:Reel




TO-262-3L/TO-262-2L包装方式

Packing Information-[TO-262-3L|TO-262-2L]

Packaging	Part Number	Quantity(pcs)	Size(mm)
Reel	Reel	800	$\Phi 330 \times \text{THK}33$
	Inner Box	800	$L355 \times W335 \times H35$
	Outer Box	7200	$L385 \times W365 \times H365$

Packaging:Reel




TO-263M包装方式

Packing Information-[TO-263M-2L]

Packaging	Part Number	Quantity(pcs)	Size(mm)
Reel	Reel	1500	$\Phi 330 \times \text{THK}25$
	Inner Box	1500	$L355 \times W335 \times H35$
	Outer Box	15000	$L385 \times W365 \times H365$

Packaging:Reel




TO-220/ITO-220包装方式

Packing Information-|TO-262-3L-D|TO-220AB|TO-220AC-A|ITO-220B|ITO-220AC|

Packaging	Part Number	Quantity(pcs)	Size(mm)
Tube	Tube	50	L534×W33×H7
	Inner Box	1000	L560×W150×H40
	Outer Box	5000	L570×W235×H175

Packaging:Tube




TO-247封装包装方式

Packing Information-|TO-247AB|TO-247AC-A|

Packaging	Part Number	Quantity(pcs)	Size(mm)
Tube	Tube	30	L495×W46×H7
	Inner Box	360	L520×W115×H58
	Outer Box	1800	L540×W320×H135

Packaging:Tube



MHCHXM[®]
Inspiring Power